


SR11 SYSTEM FOR INJECTION MOULDS WITH HEATED CHANNELS


FEATURES:




INPUTS:



OUTPUTS:



GALVANIC ISOLATION:



Export department:
Tel.: +48 68 45 75 139 /
/276/ 386
Fax: +48 68 32 54 091
e-mail: export@lumel.com.pl

LUMEL S.A.
ul. Sulechowska 1
65-022 Zielona Góra
POLAND
WWW.LUMEL.COM.PL



SR11-3



SR11-6



SR11-8

- Complete set for temperature control in injection moulds with heated channels.
- System equipped with 1 or up to 8 controllers in one housing (depending on the version).
- Built-in 15 A SSR output for each control zone (output resolution: 0.1 A).
- PID control with autotuning and Fuzzy logic algorithm ensuring a high temperature control accuracy and optimal energy consumption.
- "Soft start" function enables the mould preheating.
- Monitoring of the leakage current of heater.
- Signalling of breaks, short-circuits and inverse polarization of the sensor.
- Measurement of the heater leakage current and detection of the maximal current exceeding.
- Measurement of the load current, detection and damage signalling.
- Emergency work mode after the thermocouple damage with a mean power delivered before the damage or with the output turned off.
- RS-485 interface with MODBUS protocol (ASCII and RTU modes) for connection with PC, recorders or other Modbus devices.
- Decreased temperature mode (remote activation with logic input or local activation using the buttons).
- Relay output to signal the alarm states.

EXAMPLE OF APPLICATION



SR11 set



INPUT		
Input type	Range	Error
FE-CuNi (J)	0 .. 537 °C	≤ 0.2% of range +/- 1 digit
logic	24 V d.c.	

OUTPUTS		
Output type	Properties	Remarks
SSR relay	15 A, 230 V a.c./ heating zone	up to 8 control outputs
voltageless relay	1 A maximum 50 V a.c./d.c., NO contact	signaling of control deviation overflow

DIGITAL INTERFACE		
Type of interface	Properties	Remarks
RS-485	Modbus ASCII (8N1, 7E1, 7O1) and RTU (8N1, 8N2, 8E1, 8O1)	baud rate up to 19 200 bit/s

EXTERNAL FEATURES

Overall dimensions of the housing:	SR11-1XXXX	R11-3XXXX	SR11-6XXXX	SR11-8XXXX
Height [mm]	200	197		
Width [mm]	77.5	215	365	465
Depth [mm]	355			
Weight of the SR11 system[kg], ca.	2	7	10	12
Readout field	14 mm LED, 2 x 3 digits			
Protection grade (acc. to EN 60529)	IP30			

RATED OPERATING CONDITIONS

Supply voltage	1 zone system: 230 V a.c. +/- 10% 2 .. 8 zone system: 3 x 230/ 400 V a.c. +/- 10%	frequency 50/60 Hz +/- 10%
Temperature	ambient: 0 .. 40°C	storage: -20...70°C
Relative humidity	< 85%	inadmissible condensation
Operating position	vertical	
External magnetic field	< 400 A/m	

SAFETY AND COMPATIBILITY REQUIREMENTS

Electromagnetic compatibility	noise immunity	acc. to EN 61000-6-2
	noise emissions	acc. to EN 61000-6-4
Pollution level	2	
Installation category	III	
Maximal operating phase-to-earth voltage	for supply circuit and output circuit: 300 V	for other circuits: 50 V
Altitude a.s.l.	2000 m	

ELEMENTS OF THE SYSTEM





Fig.1. Completion of the SR11 system with ZP11 connections sets

Export department:
Tel.: +48 68 45 75 139 /
/276/ 386
Fax: +48 68 32 54 091
e-mail: export@lumel.com.pl

LUMEL S.A.
ul. Sulechowska 1
65-022 Zielona Góra
POLAND
WWW.LUMEL.COM.PL

ACCESSORIES



- 1 - ZP11-1 connection set
- 2 - ZP11-2 connection set
- 3 - ZP11-3 connection set
- 4 - ZP11-4 connection set

VIEW OF THE SYSTEM PLATE




Fig.2 Frontal plate




Fig.3. Lay-out of SR11-6XX1X system connectors.

For more information
about LUMEL's
products please visit
our website:
www.lumel.com.pl

Export department:
Tel.: +48 68 45 75 139 /
/276/ 386
Fax: +48 68 32 54 091
e-mail: export@lumel.com.pl

LUMEL S.A.
ul. Sulechowska 1
65-022 Zielona Góra
POLAND

WWW.LUMEL.COM.PL

ORDERING

System SR11 -	X	X	X	X	X
Housing dimensions:					
housing width 77.5 mm	1				
number of controllers: 1		3			
housing width 215 mm					
number of controllers: 2, 3			6		
housing width 365 mm					
number of controllers: 4, 5, 6				8	
housing width 465 mm					
number of controllers: 7, 8					
Number of controllers:					
1 controller	1				
2 controllers	2				
3 controllers	3				
4 controllers	4				
5 controllers	5				
6 controllers	6				
7 controllers	7				
8 controllers	8				
RS-485 interface:					
without RS-485 interface		0			
with RS-485 interface		1			
Connection for moulds:					
common connectors for thermocouples and heaters	1				
separate connectors for thermocouples and heaters ¹⁾	2				
Acceptance tests:					
without extra quality requirements		0			
with an extra quality inspection certificate		1			
acc. to customer's request ²⁾		X			

¹⁾ concerns only versions with 365 mm and 465 mm housing width

²⁾ after agreeing with the manufacturer

ORDERING EXAMPLE:

The code: **SR11-6 5 0 1 8** - means: system for moulds with heated channels, in a housing of 365 mm width, with 5 controllers, without RS-485 interface, with common connectors for thermocouples and heaters, without extra quality requirements.

Connection set ZP11 -	X	X	X
Kind of system:			
SR11 with 1 controller	1		
one common cable for thermocouples and heaters		2	
SR11 with 2,3,4,5,6,7,8 controllers			
one common cable for thermocouples and heaters ¹⁾		3	
SR11 with 4, 5, 6 controllers			
one cable for thermocouples		4	
SR11 with 4, 5, 6 controllers			
one cable for heaters		5	
SR11 with 7, 8 controllers			
one cable for thermocouples		6	
SR11 with 7, 8 controllers			
one cable for heaters			
Cable length:			
3 m		1	
6 m		2	
Acceptance tests:			
without extra quality requirements		8	
with an extra quality inspection certificate		7	
acc. to customer's request ²⁾		X	

¹⁾ for SR11 systems with 5, 6, 7, 8 controllers, 2 cables are required

²⁾ after agreeing with the manufacturer

ORDERING EXAMPLE:

The code: **ZP11-1 2 8** - means: connection set of ZP11 type for the SR11 system, with 1 controller for mould with heated channels, with a cable of 6 m long, without extra quality requirements.

Set of sockets for moulds GP11 -	X
Kind of socket:	
one male socket for mould and ZP11-1XX connection set	1
one male socket for mould and ZP11-2XX ¹⁾ , ZP11-4XX and ZP11-6XX ²⁾	2
one female socket for mould and ZP11-3XX and ZP11-5XX ³⁾ connection set	3

¹⁾ For cables with common wires for heaters and thermocouples, one male socket for one cable is required.

²⁾ For cables with separated wires for heaters and thermocouples, one male socket for one heater cable is required.

³⁾ For cables with separated heater and thermocouple wires, for one thermocouple cable, one female socket is required.

ORDERING EXAMPLE:

The code: **GP11- 3** - means: set of sockets for moulds of GP11 type, with one female socket for mould, for the thermocouple wire of the connection set with separated heater and thermocouple wires.

For more information about LUMEL's products please visit our website:
www.lumel.com.pl

Export department:

Tel.: +48 68 45 75 139 /
/276/ 386

Fax: +48 68 32 54 091

e-mail: export@lumel.com.pl

LUMEL S.A.
ul. Sulechowska 1
65-022 Zielona Góra
POLAND

WWW.LUMEL.COM.PL